

2-4 KG SMALL METAL GRANULE CASTING MACHINE



Details




6-12 KG METAL GRANULE CASTING MACHINE



Details




20-50 KG METAL GRANULATOR WITH GRAPHITE PLUG




Noted:

- 1. Heightened water tank
- 2. Automatic loading tray
- 3. With graphite plug

Details



20-50 KG AUTOMATIC STIR SYSTEM FOR METAL ALLOY GRAINS MAKING



Noted:

1. Heightened water tank
2. Automatic loading tray
3. With automatic stirring system


Details



6-30 KG VACUUM METAL GRANULES MAKING MACHINE




Details



50KG 100KG 150KG 250 KG PLATFORM GRANULES MAKING



Details







Parameter

Model	CDO-MG10	CDO-MG20	CDO-MG35	CDO-MG45	CDO-MG55
Power	10kw	25kw	35kw	45kw	55kw
Voltage	380V(220V), 3 phase, 50/60Hz	380V, 3 phase, 50/60Hz			
Applicable metal	Gold, K-Gold, Silver, Copper, Brass, Bronze				
Max temperature	1600℃	1600℃	1600℃	1600℃	1600℃
Melting time	2-5mins	5-8mins	10-15mins	10-20mins	20-30mins
Granulating time	About 5mins	About 10mins	About 15mins	About 20mins	About 30mins
Casting method	Gravity granulation	Gravity granulation	Gravity granulation	Gravity granulation	Gravity granulation
Max capacity	Gold: 2-4 kg Silver: 1-2 kg	Gold: 8-10 kg Silver: 4-5 kg	Gold: 40 kg Silver: 20 kg	Gold: 60 kg Silver: 30 kg	Gold: 100 kg Silver: 50 kg
Overall size(mm)	1000*500*965	1150*500*1100	1610*1550*1930	1610*1550*1930	1610*1550*1930
Weight	150kg	270kg	600kg	700kg	750kg

Features

1. Heating coil with low-voltage design, insulated heating, safe, and table.
2. The induction generator is designed to allow the homogenization of the alloy thanks to the stirring effect of the magnetic field which works while the metal is being melted in the crucible.
3. Water in the tank is continuously circulating and it is cooled by a powerful chiller to keep the process variables under control and obtaining consistency and quality in the produced grains.
4. Easy to get materials from granulating barrel and can supplement cooling water.
5. The finished products have no oxidization, producing equal particles, good color and good sphere.

Application



CDOCAST MACHINERY CO., LTD.

Skype: mandymeina
Tel: +86-15168765707

Email: sales@cdocast.com
Website: www.cdocast.com



Product Show



Gold Granule



Copper Granule



Silver Granule



More Metal

